

Can I set the TLA100 to accept the American standard for resistance values (i.e. 240 to 33 ohms) using Maretron's DSM150, DSM200, or DSM250 display?

Yes, it is possible to set the TLA100 to accept American standard resistive sensors using Maretron's DSM150, DSM200, or DSM250 display. Set the mode using Maretron's DSM150, DSM200, or DSM250 display in the following way:

1. Enter menu mode, scroll to "Configuration:" and press
2. Scroll to "Device Configuration:" and press
3. Scroll to the row containing the TLA100 and press
4. Scroll to "Tank Level Calibration:" and press
5. Scroll until you find "American Standard (240-33 ohms)" and press

Online URL:

<https://www.maretron.com/wp-content/phpkbv96/article.php?id=68>